FABORY



Slotted raised countersunk head screw DIN 964 A Steel Zinc plated 4.8 M6X60

Article number	24570.060.060
Brand	-
UBB	950353151422
UNSPSC	31161504
EAN	8715492636355
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
NEN	≈2371
BS	≈4183
ISO	≈2010
ASME	≈B18.6.7M
NF	≈E25-124

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	60
n	1.6
P	1
t (min.)	2.4

Technical Drawing

