FABORY



Slotted raised countersunk head screw DIN 964 A Steel Zinc plated 4.8 M8X40

Article number	24570.080.040
Brand	-
UBB	950353151919
UNSPSC	31161504
EAN	8715492636416
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈2371
ISO	≈2010
BS	≈4183
NF	≈E25-124
DIN	964

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	40
n	2
P	1.25
t (min.)	3.2

Technical Drawing

