
FABORY



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X40

Article number	24640.030.040
Brand	-
UBB	950353153246
UNSPSC	31161504
EAN	8715492637086
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

DIN	85
ASME	≈B18.6.7M
ISO	≈1580
BS	≈4183
NF	≈E25-128
NEN	≈1603

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if L ≤	30
k (max.)	1.8
L (mm)	40
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

