
FABORY



# Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M5X6

| | |
|---|---|
| Article number | 24640.050.006 |
| Brand | - |
| UBB | 950353604784 |
| UNSPSC | 31161504 |
| EAN | 8715492637451 |
| PKG. of 500 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M5 |
| Length | 6 mm |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Pan head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Info | N = Max. recom. static load (centr. tension) [kN]. |

## Standards

| | |
|---|---|
| DIN | 85 |
| NEN | ≈1603 |
| NF | ≈E25-128 |
| ASME | ≈B18.6.7M |
| ISO | ≈1580 |
| BS | ≈4183 |

## Technical Specification

| | |
|---|---|
| d-D | M5 |
| Thread length (min.) | 38 |
| dk (max.) | 10 |
| Full thread if L ≤ | 40 |
| k (max.) | 3 |
| L (mm) | 6 |
| n | 1.2 |
| P | 0.8 |
| t (min.) | 1.2 |

## Technical Drawing

