
FABORY



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M2,5X16

Article number	24662.025.016
Brand	-
UBB	500645204925
UNSPSC	31161504
EAN	8717077071124
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M2.5
Length	16 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	5
Full thread if L ≤	20
k	2
L (mm)	16
No. cross recess	1
P	0.45

Technical Drawing

