
FABORY



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M4X5

Article number	24662.040.005
Brand	-
UBB	951353646692
UNSPSC	31161504
EAN	8715492640116
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M4
Length	5 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	8
Full thread if L ≤	25
k	3.1
L (mm)	5
No. cross recess	2
P	0.7

Technical Drawing

