
FABORY



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M6X60

Article number	24662.060.060
Brand	-
UBB	950353755834
UNSPSC	31161504
EAN	8715492640420
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	12
Full thread if L ≤	35
k	4.6
L (mm)	60
No. cross recess	3
P	1

Technical Drawing

