FABORY



# Cross recessed countersunk head screw Phillips DIN 965 Steel Zinc plated black passivated 4.8 M2X4

| | |
|---|---|
| Article number | 24840.020.004 |
| Brand | - |
| UBB | 950353677392 |
| UNSPSC | 31161504 |
| EAN | 8715492645340 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M2 |
| Length | 4 mm |
| Class | 4.8 |
| Driving features | Phillips |
| Head shape | Countersunk head |
| Material | Steel |
| Surface treatment | Zinc plated black passivated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| DIN | 965 |
| NF | ≈E25-119-1 |
| ISO | ≈7046-1 |

## Technical Specification

| | |
|---|---|
| d-D | M2 |
| Thread length (min.) | 16 |
| dk (max.) | 3.8 |
| Full thread if L ≤ | 18 |
| k (max.) | 1.2 |
| L (mm) | 4 |
| No. cross recess | 1 |
| P | 0.4 |

## Technical Drawing

