
FABORY



Double slotted mushroom head screw NF E25-129 Steel Zinc plated 4.8 M8X80

Article number	24862.080.080
Brand	-
UBB	950353759141
UNSPSC	31162400
EAN	8715493594074
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	80 mm
Class	4.8
Driving features	Slotted
Head shape	Button head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-129

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	20
Full thread if L ≤	60
k (max.)	4.4
L (mm)	80
n	2
P	1.25
t (min.)	2

Technical Drawing

