
FABORY



Double slotted mushroom head screw NF E25-129 Steel Zinc plated 4.8 M10X60

Article number	24862.100.060
Brand	-
UBB	950353964493
UNSPSC	31161504
EAN	8715493594166
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Button head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-129

Technical Specification

d-D	M10
Thread length (min.)	38
dk (max.)	25
Full thread if L ≤	65
k (max.)	5.5
L (mm)	60
n	2.5
P	1.5
t (min.)	2.4

Technical Drawing

