FABORY



# Slotted raised countersunk head tapping screw DIN 7973 C Steel Nickel plated ST3,9X25MM

| | |
|---|---|
| Article number | 26040.039.025 |
| Brand | - |
| UBB | 950352052936 |
| UNSPSC | 31161507 |
| EAN | 8715492651488 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | 3.9 mm |
| Length | 25 mm |
| Driving features | Slotted |
| Head shape | Countersunk oval head |
| Material | Steel |
| Surface treatment | Nickel plated |
| Thread | Self tapping thread |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

## Standards

| | |
|---|---|
| NF | E25-661 C |
| DIN | 7973 C |
| BS | 4174 |
| ISO | 1483 C |

## Technical Specification

| | |
|---|---|
| D (mm) | 3.9 |
| dk | 7.5 |
| f ≈ | 1.3 |
| k ≈ | 2.3 |
| L (mm) | 25 |
| n | 1 |
| P | 1.4 |

## Technical Drawing

