FABORY



Cross recessed pan head tapping screw Phillips DIN 7981 C-H Steel Nickel plated ST3,5X25MM

Article number	26200.035.025
Brand	-
UBB	950352065490
UNSPSC	31161507
EAN	8715492652904
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	25 mm
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.6.4
DIN	7981 CH
NF	E25-658
ISO	7049 CH

Technical Specification

D (mm)	3.5
dk	6.9
k	2.6
L (mm)	25
No. cross recess	2
P	1.3

Technical Drawing

