FABORY



Cross recessed countersunk head tapping screw DIN 7982 C-H Steel Zinc plated black passivated ST3,5X9,5MM

Article number	26430.035.009
Brand	-
UBB	500654568376
UNSPSC	31162400
EAN	8712423018730
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	9.5 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Self tapping thread

Standards

ISO	7050 CH
DIN	7982 CH
NF	E25-656

Technical Specification

D (mm)	3.5
dk	6.8
k ≈	2.1
L (mm)	9.5
No. cross recess	2
P	1.3

Technical Drawing

