
FABORY



MAXXFAST Universal woodscrew cross recessed countersunk head Steel Zinc plated 4,5X30MM (25)

Article number	30000.045.030
Brand	-
UBB	500512191650
UNSPSC	31161508
EAN	8715494278898
PKG. of 200	Full Box Only

Technical Parameters

Diameter	4.5 mm
Length	30 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Info	Full boxes only.F = 9mm only if L ≥ 40mm.Diameters 3 and 3,5 are unfit for structural timber joints and therefore not CE marked.

Standards

Technical Specification

D (mm)	4.5
dk	9
F	0
k	5
L (mm)	30
No. cross recess	2
S	25

Technical Drawing

