
FABORY



MAXXFAST Universal woodscrew cross recessed countersunk head Steel Zinc plated yellow passivated 4X25MM (20)

Article number	30005.040.025
Brand	-
UBB	500512199679
UNSPSC	31161508
EAN	8715494284660
PKG. of 200	Full Box Only

Technical Parameters

Diameter	4 mm
Length	25 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Info	Full boxes only.F = 9mm only if L ≥ 40mm.Diameters 3 and 3,5 are unfit for structural timber joints and therefore not CE marked.

Standards

Technical Specification

D (mm)	4
dk	8
F	0
k	4.5
L (mm)	25
No. cross recess	2
S	20

Technical Drawing

