
FABORY



MAXXFAST Universal woodscrew cross recessed countersunk head Steel Zinc plated yellow passivated 6X50MM (35)

Article number	30005.060.050
Brand	-
UBB	500512203208
UNSPSC	31161508
EAN	8715494285025
PKG. of 200	Full Box Only

Technical Parameters

Diameter	6 mm
Length	50 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Info	Full boxes only.F = 9mm only if L ≥ 40mm.Diameters 3 and 3,5 are unfit for structural timber joints and therefore not CE marked.

Standards

Technical Specification

D (mm)	6
dk	12
F	9
k	6.3
L (mm)	50
No. cross recess	3
S	35

Technical Drawing

