FABORY



MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Stainless steel A2 ST3,5X19MM

Article number	30305.035.019
Brand	-
UBB	500618325939
UNSPSC	31161507
EAN	8715494502016
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	19 mm
Application (metal)	Aluminium
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread
Info	Full boxes only.

Standards

DIN	≈7504-O H
ISO	≈15482 H

Technical Specification

D (mm)	3.5
dk	6.9
k	2.35
L (mm)	19
L1	4
No. cross recess	2

Technical Drawing

