FABORY



# MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Stainless steel A2 ST3,5X25MM

| | |
|---|---|
| Article number | 30305.035.025 |
| Brand | - |
| UBB | 500618326192 |
| UNSPSC | 31161507 |
| EAN | 8715494502030 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | 3.5 mm |
| Length | 25 mm |
| Application (metal) | Aluminium |
| Driving features | Phillips |
| Head shape | Countersunk head |
| Material | Stainless steel |
| Material technical | A2 |
| Thread | Self tapping thread |
| Info | Full boxes only. |

## Standards

| | |
|---|---|
| DIN | ≈7504-O H |
| ISO | ≈15482 H |

## Technical Specification

| | |
|---|---|
| D (mm) | 3.5 |
| dk | 6.9 |
| k | 2.35 |
| L (mm) | 25 |
| L1 | 4 |
| No. cross recess | 2 |

## Technical Drawing

