FABORY



MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Bi-Metal ST3,9X19MM

Article number	30310.039.019
Brand	-
UBB	500618328826
UNSPSC	31161507
EAN	8715494502306
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	19 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Bi-Metal
Thread	Self tapping thread
Info	Full boxes only.

Standards

ISO	≈15482 H
DIN	≈7504-O H

Technical Specification

D (mm)	3.9
dk	8
k	2.6
L (mm)	19
L1	4.5
No. cross recess	2

Technical Drawing

