
FABORY



MAXXFAST Frame anchor nylon Plastic Nylon (polyamide) 10X165

Article number	30509.100.165
Brand	-
UBB	500619774069
UNSPSC	31162400
EAN	8715494125338
PKG. of 50	Full Box Only

Technical Parameters

Length	165 mm
Material	Plastic
Type no.	N-FAST
Info	Tinst = Tightening torque in Nm.

Standards

Technical Specification

Drill depth (min.)	55
Drill ø	10
Effective anchorage depth (hef)	50
Grip range (tfix.max.)	105
L (mm)	165
Pull-out force (N)	960
Rivet head ø	12
Shear load (N)	240
Tinst	4

Technical Drawing

