
FABORY



MAXXFAST Wall plug HammerFast Plastic Nylon (polyamide) Zinc plated 5X30MM

Article number	30510.050.030
Brand	-
UBB	500577348781
UNSPSC	31162103
EAN	8715494343275
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5 mm
Length	30 mm
Color	Grey
Material	Plastic
Surface treatment	Zinc plated
Info	Full boxes only.Allowable loads in kN are valid for screw nails with specified diameters.Allowable load includes the safety factor 5.

Standards

Technical Specification

Brick ≥ Mz12	0.2
Concrete ≥ C20/25	0.32
D (mm)	5
Drill depth (min.)	50
Drill ø	5
Grip range	5
L (mm)	30

Technical Drawing

