
FABORY



MAXXFAST Wall plug HammerFast Plastic Nylon (polyamide) Zinc plated 6X60MM

Article number	30510.060.060
Brand	-
UBB	500577349284
UNSPSC	31162103
EAN	8715494343329
PKG. of 100	Full Box Only

Technical Parameters

Diameter	6 mm
Length	60 mm
Color	Grey
Material	Plastic
Surface treatment	Zinc plated
Info	Full boxes only.Allowable loads in kN are valid for screw nails with specified diameters.Allowable load includes the safety factor 5.

Standards

Technical Specification

Brick ≥ Mz12	0.28
Concrete ≥ C20/25	0.36
D (mm)	6
Drill depth (min.)	80
Drill ø	6
Grip range	30
L (mm)	60

Technical Drawing

