
FABORY



MAXXFAST Wall plug HammerFast Plastic Nylon (polyamide) Zinc plated 8X80MM

Article number	30510.080.080
Brand	-
UBB	500577349441
UNSPSC	31162103
EAN	8715494343343
PKG. of 50	Full Box Only

Technical Parameters

Diameter	8 mm
Length	80 mm
Color	Grey
Material	Plastic
Surface treatment	Zinc plated
Info	Full boxes only.Allowable loads in kN are valid for screw nails with specified diameters.Allowable load includes the safety factor 5.

Standards

Technical Specification

Brick ≥ Mz12	0.36
Concrete ≥ C20/25	0.44
D (mm)	8
Drill depth (min.)	100
Drill ø	8
Grip range	40
L (mm)	80

Technical Drawing

