
FABORY



Spring-type straight pin slotted, light duty ISO 13337 Spring steel 420-560 HV30 5X5MM

Article number	39060.050.005
Brand	-
UBB	500645313171
UNSPSC	31163201
EAN	8717077078314
PKG. of 200	Full Box Only

Technical Parameters

Diameter	5 mm
Length	5 mm
Material	Spring steel
Material technical	420-560 HV30
Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter d ≥ 10 mm a single chamfer configuration is optional at the discretion of the manufacturer.The type of austenitic stainless spring steel is at the manufacturer’s discretion and may vary from the steel types stated in ISO 3506.V = minimum shear strength, double, in kN (valid for

Standards

DIN	7346
ISO	13337

	steel pins only).The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of slotted spring-type straight pins:These pins are used to connect two or more construction elements to each other.They are highly suitable to absorb shear forces.

Technical Specification

a	0.5
a (min.)	0.5
d1 (max.)	5.6
d1 (min.)	5.4
d2 ≈	4.4
D (mm)	5
L (mm)	5
s	0.5
V	10.4

Technical Drawing

