FABORY



Parallel key high type DIN 6885 A Steel C45+C Plain 5X5X80MM

Article number	39250.055.080
Brand	-
UBB	950359915614
UNSPSC	31163207
EAN	8715492812933
PKG. of 50	Full Box Only

Technical Parameters

Length	80 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

NEN	2430
ISO	R773
BS	4235-1
DIN	6885-A

Technical Specification

b	5
For shaft ø	12
For shaft ø ≤	17
h	5
L (mm)	80

Technical Drawing

