FABORY



# Parallel key high type DIN 6885 A Steel C45+C Plain 8X7X50MM

| | |
|---|---|
| Article number | 39250.087.050 |
| Brand | - |
| UBB | 950359081854 |
| UNSPSC | 31163207 |
| EAN | 8715492813404 |
| PKG. of 25 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Length | 50 mm |
| Material | Steel |
| Material technical | C45+C |
| Surface treatment | Plain |
| Info | Tolerance classes for dimensions b and h according to DIN 6880. |

## Standards

| | |
|---|---|
| DIN | 6885-A |
| NEN | 2430 |
| ISO | R773 |
| BS | 4235-1 |

## Technical Specification

| | |
|---|---|
| b | 8 |
| For shaft ø | 22 |
| For shaft ø ≤ | 30 |
| h | 7 |
| L (mm) | 50 |

## Technical Drawing

