FABORY



Parallel key high type DIN 6885 A Steel C45+C Plain 10X8X75MM

Article number	39250.108.075
Brand	-
UBB	950359212533
UNSPSC	31163207
EAN	8715492813817
PKG. of 25	Full Box Only

Technical Parameters

Length	75 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

ISO	R773
BS	4235-1
DIN	6885-A
NEN	2430

Technical Specification

b	10
For shaft ø	30
For shaft ø ≤	38
h	8
L (mm)	75

Technical Drawing

