FABORY



Parallel key high type DIN 6885 A Steel C45+C Plain 16X10X40MM

Article number	39250.170.040
Brand	-
UBB	950359086077
UNSPSC	31163207
EAN	8715492814548
PKG. of 10	Full Box Only

Technical Parameters

Length	40 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

NEN	2430
DIN	6885-A
ISO	R773
BS	4235-1

Technical Specification

b	16
For shaft ø	50
For shaft ø ≤	58
h	10
L (mm)	40

Technical Drawing

