
FABORY



Round head rivet DIN 660/124 Steel C4C/C10C Plain 2X5MM

Article number	39400.020.005
Brand	-
UBB	500645354415
UNSPSC	31162201
EAN	8717077082533
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	2 mm
Length	5 mm
Head shape	Round head
Material	Steel
Material technical	C4C/C10C
Surface treatment	Plain

Standards

DIN	660/124
ISO	1051
BS	4620

Technical Specification

d1	2
d2	3.5
d3 (min.)	1.87
D (mm)	2
e (max.)	1
k (js14)	1.2
L (mm)	5

Technical Drawing

