FABORY



# DIN 661/302 Steel C4C/C10C Plain 6X20MM

| | |
|---|---|
| Article number | 39410.060.020 |
| Brand | - |
| UBB | 950368009854 |
| UNSPSC | 31162201 |
| EAN | 8715492822246 |
| PKG. of 500 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | 6 mm |
| Length | 20 mm |
| Head shape | Countersunk head |
| Material | Steel |
| Material technical | C4C/C10C |
| Surface treatment | Plain |

## Standards

| | |
|---|---|
| ISO | 1051 |
| DIN | 661/302 |
| BS | 4620 |

## Technical Specification

| | |
|---|---|
| d1 | 6 |
| d2 | 10.5 |
| d3 (min.) | 5.82 |
| D (mm) | 6 |
| e (max.) | 3 |
| k ≈ | 3 |
| L (mm) | 20 |

## Technical Drawing

