FABORY



Grooved pin, full length parallel grooved with pilot DIN 1470 Free-cutting steel 8X70MM

Article number	39700.080.070
Brand	-
UBB	950359124357
UNSPSC	31163215
EAN	8715492823854
PKG. of 50	Full Box Only

Technical Parameters

Diameter	8 mm
Length	70 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only).Diameter d2 is the diameter over the grooved edges (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11.The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8739
DIN	1470
NEN	≈2601

Technical Specification

c ≈	1
d1	8
d2 ≈	8.3
D (mm)	8

Technical Drawing

L (mm)	70
r ≈	8
Tolerance	h11
V	40.5

