FABORY



Grooved pin, full length taper grooved DIN 1471 Free-cutting steel 5X40MM

Article number	39710.050.040
Brand	-
UBB	950359129489
UNSPSC	31163215
EAN	8715492824486
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5 mm
Length	40 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only).Diameter d2 is the diameter over the grooved edges (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11.The nominal length (L, tolerance class js15) does not include the rounded ends.


Standards

DIN	1471
NEN	≈2602
ISO	≈8744

Technical Specification

c ≈	0.63
d1	5
d2 ≈	5.3
D (mm)	5
L (mm)	40

Technical Drawing



r ≈	5
Tolerance	h11
V	16.5