FABORY



Grooved pin, half length taper grooved DIN 1472 Free-cutting steel 8X36MM

Article number	39720.080.036
Brand	-
UBB	950359138472
UNSPSC	31163215
EAN	8715492825636
PKG. of 50	Full Box Only

Technical Parameters

Diameter	8 mm
Length	36 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only).Diameter d2 is the diameter over the grooved edges (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11.The nominal length (L, tolerance class js15) does not include the rounded ends.


Standards

DIN	1472
ISO	≈8745
NEN	≈2603

Technical Specification

c ≈	1
d1	8
d2 ≈	8.35
D (mm)	8
L (mm)	36

Technical Drawing



r ≈	8
Tolerance	h11
V	40.5