FABORY



Grooved pin, full length parallel with chamfer DIN 1473 Free-cutting steel 2X4MM

Article number	39730.020.004
Brand	-
UBB	500645369934
UNSPSC	31163215
EAN	8717077084087
PKG. of 250	Full Box Only

Technical Parameters

Diameter	2 mm
Length	4 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only).Diameter d2 is the diameter over the grooved edges (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11.The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

NEN	≈2604
DIN	1473
ISO	≈8740

Technical Specification

c ≈	0.25
d1	2
d2 ≈	2.15
D (mm)	2

Technical Drawing

f ≈	0.9
L (mm)	4
r ≈	2
Tolerance	h9
V	2.85

