FABORY



Slotted cheese head screw DIN 84 Brass CU2/CU3 M1,4X12

Article number	48020.014.012
Brand	-
UBB	500645389999
UNSPSC	31161504
EAN	8717077096011
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.4
Length	12 mm
Driving features	Slotted
Head shape	Cylindrical head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

BS	≈4183
NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207
DIN	84
NF	≈E25-127

Technical Specification

d-D	M1.4
Thread length (min.)	25
dk (max.)	2.6
Full thread if L ≤	30
k (max.)	0.9
L (mm)	12
n	0.3
P	0.3
t (min.)	0.4

Technical Drawing