FABORY



Slotted cheese head screw DIN 84 Brass CU2/CU3 M3,5X12

Article number	48020.035.012
Brand	-
UBB	500645391466
UNSPSC	31161504
EAN	8717077096165
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3.5
Length	12 mm
Driving features	Slotted
Head shape	Cylindrical head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-127
ISO	≈1207
NEN	≈1602
DIN	84
ASME	≈B18.6.7M

Technical Specification

d-D	M3.5
Thread length (min.)	38
dk (max.)	6
Full thread if L ≤	40
k (max.)	2.4
L (mm)	12
n	1
P	0.6
t (min.)	1

Technical Drawing