FABORY



Slotted countersunk head screw DIN 963 Brass CU2/ CU3 M16X45

Article number	48170.160.045
Brand	-
UBB	500645396580
UNSPSC	31161504
EAN	8717077096677
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	45 mm
Driving features	Slotted
Head shape	Countersunk head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈2009
DIN	963
NF	≈E25-123
BS	≈4183
NEN	≈2370

Technical Specification

d-D	M16
Thread length (min.)	58
dk (max.)	29
Full thread if L ≤	70
k (max.)	8
L (mm)	45
n	5
P	2
t (min.)	3.2

Technical Drawing

