
FABORY



Hexagon flange bolt with serrated flange, DIN ≈6921 Stainless steel A2 70 M5X12

Article number	51014.050.012
Brand	-
UBB	500634383730
UNSPSC	31161620
EAN	8715494555159
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Specific features of hexagon bolts with serrated flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.The serrated flange rim gives excellent self-locking properties.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

ISO	≈4162
EN	≈1665
DIN	≈6921
ASME	≈B18.2.3.4M

Technical Specification

d-D	M5
dc (max.)	11.8
k (max.)	5.4
L (mm)	12
P	0.8
s	8

Technical Drawing

