
FABORY



Hexagon flange bolt with serrated flange, DIN ≈6921 Stainless steel A2 70 M8X16

Article number	51014.080.016
Brand	-
UBB	500634385719
UNSPSC	31161620
EAN	8715494555869
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	16 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Specific features of hexagon bolts with serrated flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.The serrated flange rim gives excellent self-locking properties.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

EN	≈1665
ISO	≈4162
ASME	≈B18.2.3.4M
DIN	≈6921

Technical Specification

d-D	M8
dc (max.)	18
k (max.)	8.1
L (mm)	16
P	1.25
s	13

Technical Drawing

