FABORY



Hexagon socket head cap screw DIN 912 Stainless steel A2 70 M14X100

Article number	51050.140.100
Brand	-
UBB	500633163638
UNSPSC	31161605
EAN	8715494610568
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	100 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

ISO	4762
NF	E25-125
ASME	B18.3.1M
NEN	1241
BS	4168-1
DIN	912

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if L ≤	55
k (max.)	14
L (mm)	100
P	2
s	12

Technical Drawing

