
FABORY



Hexalobular socket head cap screw ISO 14579 Stainless steel A2 70 M2X8

Article number	51052.020.008
Brand	-
UBB	500634396377
UNSPSC	31161605
EAN	8715494557818
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	8 mm
Class	70
Driving features	Hexalobular
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

ISO	14579

Technical Specification

b	16
d-D	M2
dk (max.)	3.8
Full thread if L ≤	16
k (max.)	2
L (mm)	8
P	0.4
Socket	6

Technical Drawing

