FABORY



Threaded rod DIN 976-1A Stainless Steel A2 70 1 mtr M3

Article number	51070.030.001
Brand	-
UBB	950353242270
UNSPSC	31161618
EAN	8715492266767
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M3
Length	1000 mm
Class	70
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.1 meter

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M3
L (mm)	1000
P	0.5

Technical Drawing

