FABORY



Threaded rod DIN 976-1A Stainless Steel A2 2 mtr 70 M14

Article number	51071.140.001
Brand	-
UBB	500633175020
UNSPSC	31161618
EAN	8715494611718
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M14
Length	2000 mm
Class	70
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.2 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M14
L (mm)	2000
P	2

Technical Drawing

