FABORY

Hexagon nut DIN 934 Stainless steel A2 METALFORM 70 M8

Article number	51089.080.001
Brand	-
UBB	950355975828
UNSPSC	31161727
EAN	8715492267887
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.Specific features of Metalform:The fixed, slightly visible dry film lubricant reduces the effect of galling.It levels out the big scatter in coefficient of friction and reduces the average value.In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform.The lubricant can easily be removed with

Standards

NF	E25-401
DIN	934
NEN	1560

	a solvent after assembly, there’s no objection against application in the food industry.

Technical Specification

d-D	M8
m	6.5
P	1.25
s	13

Technical Drawing

