FABORY



Slotted countersunk head screw DIN 963 A Stainless steel A2 large pack M1X3

Article number	51110.010.003
Brand	-
UBB	500633178255
UNSPSC	31161504
EAN	8715494612036
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1
Length	3 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
ISO	≈2009
DIN	963
ASME	≈B18.6.7M
NEN	≈2370

Technical Specification

d-D	M1
Thread length (min.)	5
dk (max.)	1.9
Full thread if L ≤	5
k (max.)	0.6
L (mm)	3
n	0.25
P	0.25
t (min.)	0.2

Technical Drawing

