FABORY



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1X5

Article number	51120.010.005
Brand	-
UBB	950353254713
UNSPSC	31161504
EAN	8715492270566
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1
Length	5 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	84
ASME	≈B18.6.7M
NEN	≈1602
NF	≈E25-127
ISO	≈1207
BS	≈4183

Technical Specification

d-D	M1
Thread length (min.)	25
dk (max.)	2
Full thread if L ≤	30
k (max.)	0.7
L (mm)	5
n	0.25
P	0.25
t (min.)	0.25

Technical Drawing