FABORY



Slotted cheese head screw DIN 84 Stainless steel A2 70 M2,5X22

Article number	51120.025.022
Brand	-
UBB	500633418669
UNSPSC	31161504
EAN	8715494600828
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2.5
Length	22 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	84
ISO	≈1207
BS	≈4183
NEN	≈1602
NF	≈E25-127
ASME	≈B18.6.7M

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	4.5
Full thread if L ≤	30
k (max.)	1.6
L (mm)	22
n	0.6
P	0.45
t (min.)	0.7

Technical Drawing