
FABORY



BILOC Prevailing torque type hexagon nut, all metal DIN ≈980V Stainless steel A2 M10

Article number	51123.100.001
Brand	-
UBB	500697353356
UNSPSC	31162400
EAN	8715492076489
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	≈980-V
ISO	≈7042

Technical Specification

d-D	M10
m (max.)	8.4
P	1.5
s	17

Technical Drawing

