FABORY



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M6X30

Article number	51300.060.030
Brand	-
UBB	950353278811
UNSPSC	31161504
EAN	8715492281630
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3
L (mm)	30
No. cross recess	3
P	1

Technical Drawing

