
FABORY



Hexalobular countersunk head screw DIN ≈965 A Stainless steel A2 M5X22

Article number	51305.050.022
Brand	-
UBB	500633228332
UNSPSC	31161504
EAN	8715494591751
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	22 mm
Class	70
Driving features	Hexalobular
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	≈965
ISO	≈14581

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	22
P	0.8
Socket	25

Technical Drawing

